

TWO critical measurements, ONE push of a button, ZERO hassle

Sindie +Cl is a two-in-one instrument enabling trace analysis of both sulfur and chlorine with one push of a button. It is the ideal solution to certify sulfur levels in finished products, assess chlorine for corrosion mitigation, and optimize process parameters.

Applications

- Total sulfur analysis from ultra low sulfur fuels to crudes
- Total chlorine analysis from aqueous solutions and aromatic products to heavy fuels, crudes, and catalyst
- For use in refinery labs, pipeline terminals, additive plants and inspection laboratories

Features and Benefits

- Sulfur
 - LOD: 0.4 ppm at 300 s.
 - Dynamic Range: 0.4 ppm to 5%
- Chlorine
 - LOD: 0.3 ppm at 300 s.
 - Dynamic Range: 0.3 ppm to 3000 ppm
- Extremely low maintenance: no conversion gasses, heating elements, columns, or quartz tubing
- Automatic sulfur correction for chlorine
- Easy to use
 - Intuitive touch screen
 - Just plug-in and measure
 - Measurement time: 30-900 s
- Fits on any bench: 37 cm (w) x 50 cm (d) x 34 cm (h).

Options


- LIMS data output software capability



ASTM, D2622,
D7039, D7536,
SH / T 0842

Trusted Precision

Sindie +Cl is powered by Monochromatic Wavelength Dispersive X-Ray Fluorescence (MWDXRF): an elemental analysis technique offering significantly enhanced detection performance over traditional XRF technology. Using the industry's most advanced optics, doubly curved crystals, Sindie +Cl achieves a high signal-to-background ratio and delivers very precise measurements of low sulfur and chlorine.



Two Critical Measurements


Sindie +Cl performs trace analysis of both sulfur and chlorine with one push of a button. You can measure both elements in one sample, or measure each separately by simply inserting a new sample.



MEASUREMENT COMPLETE	
Results - Sulfur High (%) Range	
Date: 11/02/16	Time: 13:34:49
Measurement #: 848	Unit: XOS
Description: SINDIE.CL	38 deg. C
7360 Counts	13990 Counts
3.1278 % S	1.05 PPM Cl
Re-measure	Print New

Zero Hassle

Sindie +Cl analyzes a broad range of liquid samples from aqueous solutions to the heaviest of hydrocarbons (e.g. VGO or crude oil), all without the need for dilution, combustion gasses, or other hassles like changing detectors, boats, injectors, furnaces, etc.



Product Specifications

Test Method	ASTM D7039, D2622, D7536 and SH / T 0842
Dimensions	37 cm (w) x 50 cm (d) x 34 cm (h)
Power	100-120 VAC, 47-63 HZ at 6.0 Amps/ 200-240 VAC, 47-63 HZ at 6.0 Amps
Sample Cup Volume	10 ml
I/O Ports	Ethernet 10/100 base T, RS232
Ambient Temperature Requirements	5-40° C (40-104° F)
Dynamic Range	Sulfur: 0.4 ppm - 5% Chlorine: 0.3 ppm - 3000 ppm
Measurement	User selectable: 30-900 s
Calibration	8 calibration curves. Automatic and Manual Calibration functionality



15 Tech Valley Drive East Greenbush, New York 12061 USA
PH 518.880.1500 FAX 518.880.1510 info@xos.com www.xos.com

XOS. All rights reserved. HDXRF and HD Rocksand are registered trademarks of XOS.

